

CLUTCH CUSTOM CELLULAR SHADE SPECIFICATION

Distributor	CACO, Inc. Window Fashions Johnson City, TN 37604
Headrail	The cordless cellular shade headrail is made of aluminum. The dimensions of the headrail are 1-1/2" high by 1-3/4" deep. The total depth with the installation bracket is 1-7/8". The headrail end caps are made of PVC.
Bottom Rail	The standard bottom rail is made of aluminum. The dimensions of the 9/16" bottom rail are 1/2" high by 1-5/8" deep; 3/4" bottom rail are 1/2" high by 2" deep. The bottom rail end caps are made of PVC.
Fabric	The cellular shade is made of the spun lace, non-woven fabric or woven fabric, and is 100% polyester. The fabrics are available in the single cell light filtering, double cell light filtering, Cell-In-A Cell light filtering, and single cell blackout.
Clutch Assembly	The clutch assembly consists of the clutch, tape drum support, tape drum and tape drum cover. All clutch assembly components are made of PVC. They are linked by the steel square tilt rod.
Lift Cord	Shall be braided the polyester and of sufficient length to control the raising and lowering of the shade. Outside diameter is 0.9mm.
Weight	The weight is made of 100% steel, zinc plated with double sided tape on one side.
Continuous cord	100% polyester.
Installation Bracket	The bracket is constructed of the cold rolled steel and zinc plated. The hex head screws are included.
Fire Safety	The regular cellular shade fabric is not fire retardant. The fire retardant fabric is available upon request in both light filtering and blackout.
