

CORDLESS CUSTOM CELLULAR SHADE SPECIFICATION

Distributor	CACO, Inc. Window Fashions Johnson City, TN 37604
Headrail	The cordless cellular shade headrail is made of aluminum. The dimensions of the headrail are 1-1/2" high by 1-3/4" deep. The total depth with the installation bracket is 1-7/8". The headrail end caps are made of PVC.
Bottom Rail	The standard bottom rail is made of aluminum. The dimensions of the 9/16" bottom rail are 1/2" high by 1-5/8" deep; 3/4" bottom rail are 1/2" high by 2" deep. The bottom rail end caps are made of PVC.
Fabric	The cellular shade is made of the spun lace, non-woven fabric or woven fabric, and is 100% polyester. The fabrics are available in the single cell light filtering, double cell light filtering, Cell-In-A Cell light filtering, and single cell blackout.
Cordless Module	The cordless module is constructed with the clear PVC body. The lift cord is wrapped inside the module. The steel spring provides tension to pull the shade up. A steel D rod link all modules together inside of the headrail.
Lift Cord	Shall be braided the polyester and of sufficient length to control the raising and lowering of the shade. Outside diameter is 0.9mm.
Weight	The weight is made of 100% steel, zinc plated with double sided tape on one side.
Pulling Handle	The pulling handle for the cordless shade is made of 100% PVC.
Installation Bracket	The bracket is constructed of the cold rolled steel and zinc plated. The hex head screws are included.
Fire Safety	The regular cellular shade fabric is not fire retardant. The fire retardant fabric is available upon request in both light filtering and blackout.
